


FAG FLUODX Fluorescence and Phosphorescence Colorimeter

Using invisble inks to protect your products against counterfei ng is a simple and effec ve way as you can create your own color combina ons, your own screen rulings and screen types and your own layout. No scanner in the world will be able to copy what you design. The smaller the print tolerances you can produce, the more secure the proper element will be. The FAG FLUODX is the ideal tool to support you in prin ng fluorescent or phosphorescent colors in a repeatable manner.









Fluorescence and Phosphorescence Colorimeter

FUNCTIONS




The easy to understand device user interface gives acsess to many measurement functions

PHOSPHORESCENCE




Compare phosphorescence behaviour of various samples using the FLUODXConnect Software

DESIGN AND CONTROL



FLUORESCENT COLOR



Measure the visual color impression of various samples using the FLUODXConnect Software



www.fag.ch email: sales@fag.ch Tél: + 41 21 343 23 23 Fax: + 41 21 343 23 33