




**Accurate and repeatable measurements
on large format Flexo Plates and Print.**

				
Measure	Messen	Misurare	Mesure	Medir
Film Laser Mask Flexo Plate Print	Film LAMS Maske Flexoplatte Druck	Pellicola Polimero con LAMS Polimero Stampa	Film Plaque masquée Plaque Flexo Imprimé	Película Mascara LAMS Polímero Flexo Impresión
Verify	Prüfen	Verificare	Vérifier	Verificar
Dot Area Screen Ruling Bar Code Width Dot Shape Stain Density	Flächendeckung Rasterweite Linienbreite Punktaufbau Grundscheier	Area di punto Lineatura Larghezza linea Struttura del punto Densità Stain	surface du point% Trame Largeur de la ligne Structure du point Densité Stain	Area del punto Trama/ Lineatura Ancho de linea Estructura del punto Velo de densidad
Analyze	Analysieren	Analizzare	Analyse	Analizar
Full Stochastic Screen 40LPI to 400LPI Minimum Dot	FM-Raster 40LPI bis 400LPI Kleinste Punkte	Stochastico 18LPI a 400LPI Punto minimo	Trame stochastique 18LPI to 400LPI Point plus petit	Trama estocástica 40LPI hasta 400LPI Punto menor
Documentation	Dokumentation	Documentazione	Documentation	Documentación
Statistic Quality Reports	Statistik Prüfberichte	Statistica Relazione di Qualità	Statistique Fiche de contrôle en PDF	Estadística Reporte de calidad en PDF
Calibrate	Kalibrieren	Calibrare	Calibrage	Calibrar
Reference on Glass	Referenz auf Glas	Referenza su vetro	Référence sur verre	Referencia sobre vidrio

HIGH END SOLUTIONS FOR PREPRESS AND PRINT

FLEX³XXL Flexo System Analyzer



Sample Types

Transparent Flexo Plates
Ablation Mask
Film
Non transparent Flexo Plates
Offset Plates
3D View Analysis
Print sample



Functions Set

Dot Area%
Auto Screen ruling
Dot diameter
Dot surface area
Dot perimeter
Edge factor
Stain density
Line width
Line quality index
Dot structure index
Dot height
Dot 3D diameter
Dot shoulder angle
Dot relief depth
Dot void factor
Slur factor
Mottle


Feature Set

Copy&Paste Images and Data
Compare Images
Digital Zoom x4
Dot cross section
CYM color separation
Screen angles
Mottle structure analysis
Print reports
Statistics

Find your
minimum
Dot!



Large format plates up to 200 cm x 140 cm
Mount between two tables or integrate it in to a table



RELIXP
Relief Measurement
Optional for Flex³XXL
and Flex³Pro



FLEYE+
Fast Quality Reports
Software Module

FLEX³XXL

FLEX³XXL^{PRO}

including Sensor and Fleye Software

